

Leading the World in Pressure and Temperature Measurement



Twin-Temp Thermometer
Type TT.52



Industrial Grade Bimetal Thermometer
Type TI.33



OEM Transmitter
Type A-10



Digital Pressure Test Gauge
Type CPG 1000



Standard Industrial Transmitter
Type S-10



All-welded System (AWS)
Type M93X.D1



Threaded Diaphragm Seal
Type L990.10



XSEL™ Process Gauge
Type 23X.34



General Purpose Gauge
Type 111.10



Industrial Hydraulic Gauge
Type 213.40



Industrial Gauge, All Stainless Steel
Type 23X.53

WIKA Instrument Corporation
Pressure and Temperature Measurement
1000 Wiegand Boulevard
Lawrenceville, Georgia 30043
Toll Free 1-888-WIKA-USA (945-2872)
Tel (770) 513-8200 • Fax (770) 338-5118
www.wika.com • info@wika.com

Please visit www.wika.com for datasheets and complete application information.

