Product Catalog 800









Table of Contents

Selecting a Pressure Gauge	3
Chemical Compatibility Table	5
Advantages of Liquid-Filled Gauges	6
WIKA Part Numbers	7
Ordering Guidelines for	
Pressure Gauges	8

MECHANICAL PRESSURE	
Commercial Gauges	9
111.10 1½", 2", 2½", 4"	10
111.10SP - Fire Sprinkler 4"	13
111.10 & 111.12 1½", 2", 2½"	14
111.12 1½", 2", 2½" 3½", 4"	16
111.11 1½", 2", 2½"	19
111.11RF - Refrigeration 21/2"	20
111.16PM 1½", 2"	21
111.11PM 2½"	22
111.25CT 4½"	23
113.13 1½", 2½"	24
Additional 100 Series	
Options & Accessories	25

Industrial & Process Gauges	27
131.11 1½", 2"	28
1X1.15 2", 2½"	29
13X.53 4"	30
2X1.11 10"	31
212.20 6"	32
213.40 2½", 4"	33
21X.40PM 3½"	36
21X.53 2", 2½", 4"	37
23X.53 2", 2½", 4"	42
21X.54 2½", 4"	45
23X.54 2½, 4"	46
233.55 2½"	50
23X.30 2½", 4"	51
23X.50 2½", 4", 4½", 6"	53
21X.34 4½"	56
22X.34 4½"	57
23X.34 4½", 6"	58
26X.34 4½"	61
232.34DD 4½"	62
212.25 4½", 6"	63
232.25 4½", 6"	64
Sealgauge® Principles	65
42X.12/43X.12 4", 6"	66
43X.30 4", 6"	67
43X.36 4", 6"	68
43X.50 4", 6"	69
45X.50 4", 6"	70
43X.56 4", 6"	71

438.50 4", 6"	71
Low Pressure Gauges	73
6X1.10 2", 2½"	74
611.13 2", 21/2"	75
612.20 4"	76
6X2.34 4½"	77
63X.50 2½", 4", 6"	78

Differential & Duplex Gauges	79
700.04 21/2", 41/2"	80
700.05 21/2", 41/2"	81
7X1.12 4", 6"	82
732.14 4", 6"	83
712.25DP 4½", 6"	85
712.25DX 4½", 6"	86
716.11 21/2", 4", 6"	87
732.25 41/2", 6"	88
732.26 41/2", 6"	89
732.51 4", 6"	90
High Precision Gauges	91
312.20 6"	92
332.30 6"	93
332.34 41/2"	94
332.54 4"	95

Calibration Test	
Equipment & Accessories	97
CPP30	98
CPP1000-M	98
65-2000 & 65-2000 II	99
CPH-6200	100
CPH-6000	100

ELECTRONIC PRESSURE

Electronic Measurement

MEASUREMENT

96

101

102

342.11 10"

Industrial Pressure Transmitters	105	
S-10/S-11	106	
IS-20/IS-21/IS-20-F/IS-21-F	115	
F-20/F-21	127	
HP-1	135	
PSD-10	136	
OEM Pressure Transmitters	143	
C-10	144	
A-10	150	
ECO-1	156	
N-10/N-11	161	
E-10/E-11	169	
MH-1	177	
MH-2	179	
OT-1	184	
OC-1	189	
TTF-1	189	
3A Sanitary & Submersible		

1117-1	169	
3A Sanitary & Submersible		
Transmitters	191	
S-10-3A	192	
F-20-3A	194	
SA-11	198	
LS-10/LH-10	200	
IL-10	207	

Special Purpose Transmitters	209
UT-10/UT-11	210
DG-10	218
P-10, P-11	224
DP-10	225
Meters & Displays	229
907.50.9X0	230
A-AI-1	233
DI-15	235
TRONIC LINE Miscellaneous	
Accessories & Replacement	
Parts List	237
DIAPHRAGM SEALS	239

Assembled Seals	245
M93X.25	246
M93X.3A	249
M93X.2C	252
M990.30	255
M93X.D1	257
Threaded Seals	261
L990.TA	262
LOGGETE	004

Till Caaca Ocalo	
L990.TA	262
L990.TB	264
L990.10	267
L990.TC	270
L990.14	273
L990.40	275
L990.34	278
L990.36	280

Flanged Seals	283
L990.12	284
L990.FA	287
L990.FC	290
L990.FD	293
L990.FB	296
L990.26	299
L990.27	302
L990.FR	305
L990.28	308
L990.29	311
L990.35	313
L990.41	315

Sanitary Seals

L990.18

L990.22 L990.57 L990.58 L990.SD	322 324 326 328
Plastic Seals	331
L990.31	332
L990.PA	334
L990.PF	335

319

320



INLINE Seals™

Table of Contents continued

337

L981.10	338
L981.18	341
L981.22	343
L981.27	346
L981.31	349
L981.57	351
L981.SY	353
Capsule Seals	355
L970.10	356
L970.11	357
Seal Accessories	359
910.27	360
L910.ZA	362
General Seal Information	365
MECHANICAL TEMPERATURE	373
Bimetal Thermometers	374
TI.1005	376
TI.ST	377
TI.T20/TI.T17	378
TI.20	380
TI.30/TI.50	381
TI.31/TI.51	382
TI.32/TI.52	383
TI.33/TI.34/TI.53/TI.54	384
TI.33/TI.34/TI.53/TI.54	384
TI.33/TI.34/TI.53/TI.54 Bimetal Thermometer Options	384 387
Bimetal Thermometer Options	387
Bimetal Thermometer Options Digital Thermometers	387
Bimetal Thermometer Options Digital Thermometers TI.1006DW	387 389 390
Digital Thermometers TI.1006DW TI.80/TI.82	387 389 390
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers	387 389 390 391
Digital Thermometers TI.1006DW TI.80/TI.82	387 389 390 391 393 394
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52	387 389 390 391
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82	389 390 391 393 394 399
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers	387 389 390 391 393 394 399
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers TI.R45/TI.R60	387 389 390 391 393 394 399 401 404
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers	387 389 390 391 393 394 399
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers TI.R45/TI.R60 TI.TSG60	387 389 390 391 393 394 399 401 404 408
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers TI.R45/TI.R60 TI.TSG60 Vapor Actuated Thermometers	389 390 391 393 394 399 401 404 408
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers TI.R45/TI.R60 TI.TSG60	387 389 390 391 393 394 399 401 404 408
Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers TI.R45/TI.R60 TI.TSG60 Vapor Actuated Thermometers TI.V20/TI.V25/TI.V35/TI.V45	389 390 391 393 394 399 401 404 408
Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers TI.R45/TI.R60 TI.TSG60 Vapor Actuated Thermometers TI.V20/TI.V25/TI.V35/TI.V45 Industrial Glass Thermometers	387 389 390 391 393 394 399 401 404 408 411 412
Bimetal Thermometer Options Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers TI.R45/TI.R60 TI.TSG60 Vapor Actuated Thermometers TI.V20/TI.V25/TI.V35/TI.V45 Industrial Glass Thermometers TI.61102/TI.61104	387 389 390 391 393 394 399 401 404 408 411 412
Digital Thermometers TI.1006DW TI.80/TI.82 Twin-Temp Thermometers TT.30/TT.32/TT.50/TT.52 TT.80/TT.82 Gas Actuated Thermometers TI.R45/TI.R60 TI.TSG60 Vapor Actuated Thermometers TI.V20/TI.V25/TI.V35/TI.V45 Industrial Glass Thermometers	387 389 390 391 393 394 399 401 404 408 411 412

Thermowells	425
TW.TH (Threaded)	429
TW.SW (Socket/Weld)	434
TW.FL (Flanged)	436
TW.SC (Sanitary)	437
Industrial Glass	439

ELECTRONIC TEMPERATURE	
TRANSMITTERS	441
T19.10	442
T19.30	442
T23.10	443
T24.10	443
T12.10	444
T12.30	445
T32.10/T32.30	446
T42.10	447

ACCESSORIES	449
910.10 Gauge Cocks	450
910.11 Needle Valves	451
910.11.100 Mini-Needle Valves	452
910.11.200 Block & Bleed Valves	453
910.11.300 Multi-Port Valves	454
910.12.100/910.12.200/	
910.12.300 Snubbers	455
910.13 Overpressure Protectors	456
910.14.100 Test Port Plug	457
910.14.200 Adaptors	458
910.14.300 Couplings	459
910.15.100/910.15.200 Siphons	460
CP3000/CP4000 Alarm Contacts	461
Socket Restrictor	464
Drag Pointer	464
Alarm Contacts	464

471

GENERAL INFORMATION

423

Sealgauge® and INLINE SEAL™ are registered trademarks of WIKA Instrument Corporation. Halocarbon® is a registered trademark of the Halocarbon Products Corporation. Hastelloy® is a registered trademark of the Cabot family of companies. Fluorollube® is a registered trademark of the Hooker Chemical & Plastics Corporation. Monel®, Inconel®, Incone

TI.D01



Selecting a Pressure Gauge

When selecting a pressure gauge, it is important to consider the following factors to ensure safety and accuracy:

- 1. Pressure fluid composition
- 2. Pressure fluid temperature
- 3. Ambient conditions
- 4. Pressure range
- 5. Conditions affecting wear of the system
- 6. Method of mounting
- 7. Required accuracy

Pressure fluid composition

Since the sensing element of a pressure gauge may be exposed directly to the measured medium, consider the characteristics of this medium. It may be corrosive, it may solidify at various temperatures, or it may contain solids that will leave deposits inside the sensing element. For pressure fluids that will not solidify under normal conditions or leave deposits, a Bourdon tube gauge is acceptable. Otherwise a Sealgauge® or diaphragm seal should be used. A chemical compatibility chart follows this section to aid in the selection of the proper sensing element material.

Pressure fluid temperature

Steam and other hot media may raise the temperature of the gauge components above safe working limits of the sealed joints. In these cases it is recommended that a siphon, cooling tower or diaphragm seal be used in conjunction with the pressure gauge.

Ambient conditions

The normal ambient temperature range for WIKA pressure gauges is -40°F to +140°F (-40°C to +60°C) for dry or silicone-filled gauges and -4°F to +140°F (-20°C to +60°C) for glycerine-filled gauges. The error caused by temperature changes is +0.3% or -0.3% per 18°F rise or fall, respectively. The reference temperature is 70°F (20°C). The correction is for the temperature of the gauge, and not the temperature of the measured medium. Remote gauge mounting using a diaphragm seal and capillary line is one alternative for applications involving extreme ambient temperature.

Moisture and weather effects must also be considered. Liquid-filled gauges prevent condensation build up. For outdoor use, stainless steel, brass, or plastic cased gauges are recommended.



A g

Pressure range

A gauge range of twice the working pressure is generally selected. The working pressure in all cases should be limited to 75% of the gauge range. Where alternating pressure and pulsation are encountered, working pressure should be limited to 2/3 of the gauge range.

5

Conditions affecting wear of the system

In applications involving severe pressure fluctuation or pulsation, the use of restrictors and/or snubbers is recommended. In addition, liquid-filled gauges increase the service life of gauges in these conditions. WIKA liquid-filled gauges are generally filled with glycerine. Silicone for larger temperature extremes and Halocarbon® for use with oxidizing agents such as chlorine, oxygen, and hydrogen peroxide are also available.

6

Method of mounting

Radial (LM) and back (CBM or LBM) connections are available for most WIKA gauges. WIKA stocks gauges with standard NPT threaded connections. Other types such as metric threads, straight threads, hose barbs, and special fittings are available as a special order.

Pressure gauges should be mounted in the upright position. For applications where the gauge is mounted sideways, horizontally, or upside down, contact WIKA Customer Service for gauge type compatibility.

Required accuracy

WIKA stocks gauges with accuracies from \pm 3/2/3% to \pm 0.1% of span (ASME Grade B to Grade 4A).

7

To ensure safe and accurate gauge selection, you must take all of the above factors into consideration. When in doubt, please do not hesitate to contact your local stocking distributor or WIKA Customer Service for assistance!

1-888-WIKA-USA



Chemical Compatibility Table

Acetic Acid	В	Ethyl Acetate	Α	Oxygen	Α
Acetic Anhydride	D	Ethyl Cellulose	В	Paraffin	Α
Acetone	В	Ethylene	A	Phosphoric Acid	В
Acetylene	В	Ethylene Dibromide	В	Photographic Solutions	В
Alcohol	A	Ethylene Dichloride	D	Pickling Solutions	В
Alums	В	Ethylene Glycol	Α	Picric Acid	В
Aluminum Sulfate	В	Ferric Nitrate	В	Picric Acid (dry)	В
Ammonia	В	Ferric Sulfate	В	Potassium Chloride	D
Ammonium Carbonate	В	Formaldehyde	В	Potassium Cyanide	В
Ammonium Hydroxide	D	Freon	Α	Potassium Permanganate	В
Ammonium Phosphate	D	Gallic Acid	В	Prestone	Α
Beer	Α	Gas (for lighting)	Α	Salicylic Acid	Α
Benzine	Α	Gasoline	Α	Sea Water	С
Benzol	Α	Gasoline (refined)	В	Silver Nitrate	В
Benzyl Alcohol	В	Glucose	С	Sodium Carbonate	D
Bleach Liquors	В	Glycerine	Α	Sodium Cyanide	D
Bordeaux Mixture	Α	Hydrocyanic Acid	В	Sodium Hydroxide	D
Butane	В	Hydrogen	В	Sodium Nitrate	В
Butanol	Α	Hydrogen Peroxide	В	Sodium Peroxide	В
Butyric Acid	В	Kerosene	Α	Sodium Phosphate	В
Calcium Bisulfite	В	Lacquers	Α	Sodium Sulfate	В
Calcium Chloride	С	Lactic Acid	В	Sodium Sulfide	D
Calcium Hydroxide	В	Lysol	В	Sodium Sulfite	В
Carbon Dioxide(dry)	В	Magnesium Hydroxide	С	Sulfur Dioxide	D
Carbon Bisulfide	В	Magnesium Sulfate	В	Sulfur Dioxide (dry)	В
Casein	В	Mercury	В	Sulfuric (75%)	В
Chloroform	В	Methyl Chloride	D	Sulfurous Acid	В
Chromic Acid	В	Methyl Salicylate	D	Tanning Liquors	D
Citric Acid	В	Naphtha	Α	Toluene	Α
Coal Gas	Α	Nickel Acetate	В	Vegetable Oils	В
Copper Sulfate	В	Nitric Acid (pure)	В	Vinegar	В
Cottonseed Oil	В	Nitrous Acid	D	Water	Α
Creosote (crude)	В	Nitrous Oxide	D	Whiskey	В
Dextrine	Α	Oil (lubricating)	Α	Wines	В
Ethers	D	Oil (refined)	Α	Zinc Sulfate	В

NOTE: For steam service, a siphon is required.

Find the process fluid in the table above and match the letter code (A,B,C, or D) with the wetted part material listed below:

A = Brass (Copper Alloy) C = Monel®

B = 316 Stainless Steel D = Consult Factory

This table is provided as a reference only and is accurate to the best of WIKA's knowledge. WIKA assumes no responsibility for, or obligation from, the information here.



Advantages of Liquid-Filled Gauges

Liquid-filled gauges

Liquid-filled pressure gauges provide a number of advantages:

- * the liquid absorbs vibration and pressure spikes
- the dampening action of the liquid enables the operator to take readings during conditions of rapid dynamic loading and vibration
- the liquid lubricates all moving elements, dramatically reducing wear in the movement
- * because most liquid-filled gauges are filled with non-aqueous liquid and hermetically sealed, they perform in corrosive environments and are immune to moisture penetration and icing, and shock effects are lessened

Liquid-filled gauges enhance the reliability and integrity of the measuring system for long periods under extreme operating conditions.



Indicates liquid-fillable pressure gauge.

Liquid Fill Fluid

Ambient Temperature Ratings (Table A)

Allowable Operating Range - Temperature range in which the operation of the gauge is not adversely affected by the filling liquid. At temperatures above the maximum rating, the fluid may break down. At temperatures below the minimum rating, the fluid may solidify (freeze).



NOTE: Some parts of the pressure gauge may not be able to withstand temperatures above 140°F. Consult with the factory for technical assistance for these applications.

Choose the Right Liquid

The type of liquid used to fill the gauge varies with the application. Although pure glycerine provides the best performance in most applications, each has its own requirements. Guidelines to help ensure that a fluid is properly matched to an application are:

- if icing is a problem, use gauges filled with silicone oil or other comparable liquids. They have low viscosities even at -60°C
- * if the system has electric accessories, such as contacts, use insulating oils, and
- * if extreme temperature fluctuations are expected, use silicone oils

The higher the liquid viscosity, the greater its dampening capacity. The reason for this is that dampening changes in proportion to the temperature-dependent viscosity of the filling liquid. The suitable degree of dampening depends on the operating requirements the gauge must meet, such as pointer response time, pressure extremes, vibration, and changes in pressure. WIKA can recommend specific liquids to suit problem applications.

Fill Fluid	Allowable Operating Range
Glycerine Dow 99.7% USP, Synthetic 1118 Centistokes at 68°F	-4°F to 140°F -20°C to 60°C
Silicone Dow Corning 200 Fluid 1000 Centistokes at 77°F	-40°F to 140°F -40°C to 60°C
Halocarbon® Halocarbon® Products 6.3 Centistokes at 100°F	-40°F to 140°F -40°C to 60°C

Table A - Allowable Ambient Temperature Ratings

Liquid-Filled Gauge Case Venting

For pressure gauges with full scale ranges of 300 psi and below (including vacuum and compound ranges of 30" Hg-0-200 psi and below), case venting (after the gauge is installed) is necessary to preserve the accuracy. Temperature fluctuations during shipment and in the process application cause the liquid filling to expand and contract which in turn increases or decreases case pressure. As a result, accuracy can be decreased and the pointer may not return to zero properly until the gauge is vented to the atmosphere.

To vent a WIKA gauge, move the valve to the open position which will release any pressure or vacuum built up in the case. If the gauge is installed in an upright position, the lever can be left in the open position. The lever allows the use of a gauge in a non-upright orientation.



Vent Plug



WIKA Type Numbers

The following is a guide to the WIKA model numbering system.

2 1 3 4 0

WETTED PARTS

(Parts in contact with the fluid)

- 0 = Special design
- 1 = Copper alloy (brass)
- 2 = Steel
- 3 = Stainless steel
- 4 = Nickel iron alloy (Ni-Span C®)
- 5 = Plastic (Refers to coating or lining, not actual sensing element)
- 6 = Nickel copper alloy (Monel®)

BASIC INSTRUMENT TYPE (Instrument Series)

- 1 = Standard General Purpose Design
- 2 = High Quality Industrial Design
- 3 = Test & Precision Test Gauges
- 4 = Sealgauge® Diaphragm Gauges
- 5 = Absolute Pressure Gauges
- 6 = Capsule Pressure Gauges (Low pressure)
- 7 = Differential Pressure and Duplex Gauges
- 8 = TRONIC Line
- 9 = Diaphragm Seals

CASE FILLING

- 0 = Special type
- 1 = Standard type
- 2 = Increased water protection (splash resistant) - dry case
- 3 = With liquid filled case or ready-to-be filled
- 4 = Square or rectangular housing

DESIGN FEATURES

- 10 = Standard design (lower mount connection in "100 series")
- 11 = Compressed gas gauges or small size stainless steel
- 12 = Standard design (center back mount connection in "100 series")
- 13 = Liquid-filled ABS plastic case
- 15 = Special stainless steel gauge
- 20 = Heavy duty case, usually with bayonet ring, separate lens and increased dust and water spray protection
- 25 = Hinged ring design
- 30 = Solid-front, blow-out back case (safety case).
- 34 = Fiberglass reinforced thermoplastic case "Process Gauge"
- 40 = Forged brass case.
- 41 = Special design for mining industry
- 50 = All stainless construction
- 52 = Gas density monitor or controller
- 53 = Stainless case, o-ring or welded connection to socket, crimped ring bezel
- 54 = Stainless case, o-ring or welded connection to socket, bayonet ring

SPECIAL FEATURES

Some products may have additional letters in the type code. This typically indicates a special feature or application



Ordering Guidelines for Pressure Gauges

1) "Quick Order" 7- or 8-Digit Part Numbers:

Example: 9834850

Use the part number for the instrument you wish to order.

If you need additional options, or don't see a part number referenced for the exact product you need, you may use "DESCRIPTIVE TEXT" as indicated below (see #2). **A 7-or 8-digit part number will be provided with your Order Confirmation.** The part number provided may then be used for re-ordering purposes.

2) Descriptive Text Part Number System:

Example:

Standard Product Description Section

232.34
4.5
100 psi
1/2"
LM
SG, PM
(Typel #) (Dial Size) (Pressure Range) (Process Conn. & Location) (Additional Options / Accessories)

The above example would indicate a 4 ½" process gauge, dry, 100 psi dial scale, ½" NPT connection, lower mount connection with the following selected options: safety glass (SG) and panel mount (PM), as indicated.

- Descriptive text can be used anytime you do not find an exact item with a listed part number. You may add as many codes at the end of the descriptive text as is required to configure the product.
- CODES and installed prices are found on a selection chart for each Model Type.
 Additional options may be located on the Accessory pages section in the back of the Catalog 700.
- Please reference the WIKA Type Number (pg. 7) for additional Model/Type information.
 WIKA Model Types may already determine many configurations for wetted parts and case fill.
- Options and Accessories should always appear at the end of the Descriptive Text, separated by commas. If you are not sure what to use for abbreviated code, then simply SPELL IT OUT.

NOTE: If you provide a part number and descriptive text, we will use the part number only.

If you are unclear, do not see the option(s) needed, or require ordering assistance, please contact a WIKA Customer Care or Technical Quote Team Representative.